# PRODUCT INFORMATION PACKET

Model No: D135
Catalog No: D135
Fan and Blower Motor, 1/25 HP, 1 Ph, 60 Hz, 115 V, 1500 RPM, 1 Speed, 3.3" Diameter, TEAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E

## Nameplate Specifications

| | | | |
|---|---|---|---|
| Phase | 1 | Output HP | 1/25 Hp |
| Output KW | 0.03 kW | Voltage | 115 V |
| Speed | 1500 rpm | Service Factor | 1 |
| Frame | 3.3 | Enclosure | Totally Enclosed Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 1.70 A |
| Duty | Air Over | Insulation Class | B |
| UL | Recognized | CSA | Y |
| CE | N | Number of Speeds | 1 |

## Technical Specifications

| | | | |
|---|---|---|---|
| Electrical Type | Shaded Pole | Starting Method | Across The Line |
| Poles | 4 | Rotation | Counterclockwise Shaft End |
| Mounting | Extended Studs | Drive End Bearing | Sleeve |
| Opp Drive End Bearing | Sleeve | Frame Material | Steel |
| Shaft Type | Flat | Overall Length | 6.64 in |
| Frame Length | 2.57 in | Shaft Diameter | 0.313 in |
| Shaft Extension | 2.30 in | | |
| Connection Drawing | NA | Outline Drawing | 7163194322_S001 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:07/31/2026

Uncontrolled Copy

BROWNING MANUFACTURING COMPANY, MAYSVILLE, KENTUCKY

| | |
|---|---|
| DATE | 4-9-65 |
| DR. | BL. |
| CH'K'D | |
| DISTRIBUTION | |

8.000 O.D. 2 GR "B", 3.500 O.D. 4 GR "B" x 1 5/8 B. SPCL. STEPCONE SHEAVE

NEW YORK AIR BRAKE CO.

MATERIAL 8 1/2" C.I. STICK

PART NO.

BALANCE "STD.

FINISH "STD. GRAY"

MARKING — YES: 7 7 — NO: 7

BROWNING

SIZE


PART NO.

TOLERANCES
UNLESS OTHERWISE SPECIFIED
FRACTIONAL DIMENSIONS ±1/64
DECIMAL DIMENSIONS ±.005

REVISION | BY | DATE

REVISION | BY | DATE

REVISION | BY | DATE




| APPROVAL | NO APPROVAL REQUIRED | DWG. NO. | ISSUE |
|---|---|---|---|
| SENT TO EDWARDS IND. | | NA-3002 | |
| SENT 4/9/65 RET'D 4-14 | PER DATE | | |

FORM 14C