Tower | E30182-01BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A box of UV-rated acrylic is constructed of precise miter cut corners and silk screened white on its interior to form a tower of evenly distributed LED illumination. For wet locations, the LED light source is completely sealed and provides softer omnidirectional illumination to add security and sufficiently brighten spaces. The die cast aluminum frame is finished in a black outdoor rated powder coat for longer lasting color in outdoor settings.



*height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 8" W x 15" H x 4" Ext
BACK PLATE	: 8" W x 13.4" H x 7.5" HCO
HANGING WEIGHT	: 5.03 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,200 Rated (1,170 Del.)
BULB	: 1 x 15W LED PCB Integrated , 15W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Black (BK)

GLASS

White 01

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com