

CAILYN

HL1157201-AGB/CFK

This charming little lamp features playful proportions and tactile materials. A scalloped raffia shade is paired with a ceramic base in a Frost Crackle glaze. The natural texture softens the silhouette, which is approachable and full of character. Aged Brass hardware adds a finishing note to Cailyn.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

AGED BRASS w/ Ceramic Frost Crackle

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 12.5"

Width/Diameter: 10"

Canopy/Backplate: 2.75"

Product Weight: 4lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Natural Raffia

Shade 1 Top Width: 4.75"

Shade 1 Bottom L/W: 0" / 10"

Shade 1 Height: 8.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A15

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 96"

Cord Type: SPT-2 BLACK FABRIC

Switch Type: ON/OFF LINE SWITCH ON CORD

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 13" x 13" x 17"

Carton 1 Weight: 8lb

Shipping Method: Ground

Country of Origin: VN

