
Celeste | E30322-112BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

Celeste brings an ethereal glow to outdoor architecture through luminous cast glass and quiet modern framing. A clear and white swirl glass panel appears almost celestial when illuminated, revealing soft monvement, layered texture, and atmospheric depth. Set within a non-corrosive aluminum frame in Matte Black, the design balances artistry with durability for exterior spaces. Select from 5 color temperatures that range from a warm 2700K to a bright 5000K. Wet rated and offered in 16" and 24" heights, Celeste creates a refined statement for entries, patios, corridors, and modern facades.



MEASUREMENTS

DIMENSION	: 5.5" W x 16" H x 2" Ext
MAX OAH	: 5.5" W x 5.5" H
HANGING WEIGHT	: 4 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,800 Rated (1,500 Del.)
BULB	: 1 x 19.5W LED DC Integrated , 20W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1 Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: All

FINISHES OPTION

Black (BK)

GLASS

White Spiral 112

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Vertical
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com