

CONTINUOUS HINGE WITH 3-POINT LATCH, TYPE 4



APPLICATION

These time-tested, single-door enclosures feature Hoffman’s exclusive padlocking POWERGLIDE Handle with 3-point latching for quick and convenient access. Ideal for indoor and outdoor applications, these rigid-bodied enclosures provide superior ease-of-access without sacrificing a secure seal.

BULLETIN: A4W3

Catalog Number	Height (in.)	Width (in.)	Depth (in.)
A16H16ALP3PT	16	16	6
A20H16ALP3PT	20	16	6
A24H24ALP3PT	24	24	6
A20H16BLP3PT	20	16	8
A20H20BLP3PT	20	20	8
A24H20BLP3PT	24	20	8
A24H24BLP3PT	24	24	8
A30H24BLP3PT	30	24	8
A30H30BLP3PT	30	30	8
A36H30BLP3PT	36	30	8
A36H30CLP3PT	36	30	10
A36H30DLP3PT	36	30	12
A48H36DLP3PT	48	36	12
A60H36DLP3PT	60	36	12
A72H36DLP3PT	72	36	12
A48H36FLP3PT	48	36	16
A60H36FLP3PT	60	36	16
A72H36FLP3PT	72	36	16
A60H36GLP3PT	60	36	18
A72H36GLP3PT	72	36	18
A60H36JLP3PT	60	36	24
A72H36JLP3PT	72	36	24

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12, 13; File No. E61997
 cUL Listed per CSA C22.2 No. 94; Type 4, 12, 13; File No. E61997

NEMA/EEMAC Type 3, 4, 12, and 13
 CSA, File No. 42186: Type 4 and 12
 IEC 60529, IP66

CONTINUOUS HINGE WITH CLAMPS LP, TYPE 4



Catalog Number	Height (in.)	Width (in.)	Depth (in.)
A24H16ALP	24	16	6
A24H20ALP	24	20	6
A24H24ALP	24	24	6
A30H20ALP	30	20	6
A30H24ALP	30	24	6
A36H24ALP	36	24	6
A16H12BLP	16	12	8
A20H16BLP	20	16	8
A20H20BLP	20	20	8
A20H24BLP	20	24	8
A24H20BLP	24	20	8
A24H24BLP	24	24	8
A24H30BLP	24	30	8
A30H20BLP	30	20	8
A30H24BLP	30	24	8
A30H30BLP	30	30	8
A36H24BLP	36	24	8
A36H30BLP	36	30	8
A42H30BLP	42	30	8
A42H36BLP	42	36	8
A48H36BLP	48	36	8
A60H36BLP	60	36	8
A20H16CLP	20	16	10
A24H20CLP	24	20	10
A30H24CLP	30	24	10
A36H30CLP	36	30	10
A48H30CLP	48	30	10
A48H36CLP	48	36	10
A60H36CLP	60	36	10
A30H24DLP	30	24	12
A36H30DLP	36	30	12
A48H36DLP	48	36	12
A36H30FLP	36	30	16
A48H36FLP	48	36	16
A60H36FLP	60	36	16

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12, 13; File No. E61997
 cUL Listed per CSA C22.2 No. 94; Type 4, 12, 13; File No. E61997

NEMA/EEMAC Type 3, 4, 12, and 13
 CSA, File No. 42186: Type 4 and 12
 IEC 60529, IP66

APPLICATION

These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.

BULLETIN: A4

Catalog Number	Height (in.)	Width (in.)	Depth (in.)
A16H12ALP	16	12	6
A16H16ALP	16	16	6
A16H20ALP	16	20	6
A20H16ALP	20	16	6
A20H20ALP	20	20	6
A24H12ALP	24	12	6