



Clarity 6A TracJack, ETL verified to TIA Category 6a component specification. Front-loading and front removable. Universal T568A/B wiring label and tapered wiring towers simplify termination. Tuned to Cat6a Clarity patch cords for optimum performance

## Features & Benefits

ETL Verified to Category 6A component standard: Ensures standards compliance.

Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.

Center tuned design: Transparent interface with Clarity 6A/10G cords

Easy lace IDC housing: Reduces wiring time

Standard TracJack footprint: Fits in all TracJack faceplates and housings

Icon compatible, C6A marking on jack face: Supports 606 designation requirements

## Specifications

### General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875855545	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	TIA-568.2-D, 802.3bt Type 3 and Type 4, UL 1863, IEC-603-7 compliant, IEEE 802.3af / 802.3at, FCC part 68 Subpart F
Warranty Type	5-Year	Type	Jack

### Dimensions

Product Width US	0.73 in	Product Depth US	1.1 in
Product Height US	0.92 in		

---

## Additional Information

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

## Technical Information

---

Wire Gauge	22-24 AWG	Termination Style	110
------------	-----------	-------------------	-----

---

Connector Type	RJ-45	Impedance	100 Ohm
----------------	-------	-----------	---------

---