Alumilux Line 5CCT | E42342-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

An update to our popular Line series, the Line 5CCT uses a wider profile of aluminum with adjustable color temperatures. Simply toggle between the 5 settings: 2700-3000-3500-4000-500K to suit the space where it is installed. Following the original design's premise, the Line is a straight and flat bar that indirectly casts light indirectly on the surface behind it.



MEASUREMENTS

DIMENSION	: 24" L 4.5" H x 2.75" Ext
BACK PLATE	: 4.5" W x 4.5" H x 12" HCO
HANGING WEIGHT	: 2.42 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,800 Rated (1,250 Del.)
BULB	: 2 x 6.5W LED AC Integrated , 13W Total
BULB INCLUDED	: (Integrated)
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

- Architectural Bronze (ABZ)
- Black (BK)
- Satin Aluminum (SA)
- White (WT)

MATERIAL

Aluminum, PC

RATINGS

cETLus
Wet Location
CA Title 24
ADA

ADDITIONAL

INSTALL UP/DOWN: Vertical
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com