



QSW-M2106-4C

Management Type	Web Managed
Number of Ports	10
10GbE SFP+/RJ45 Combo Ports	4
2.5GbE (RJ45)	6
Power Supply Description	Adapter
Max. Power Consumption	36W
Input Power Type	DC
Input Voltage Range	12V/3A
MAC Address Table	16K
Total Non-Blocking Throughput	55Gbps
Switching Capacity	110Gbps
Management Interface	Web
Console	RJ45
Energy Efficient Ethernet (IEEE 802.3az complaint)	Yes
Fan	PWM double ball bearing fan x 1

Supported Standards	IEEE 802.3 Ethernet IEEE 802.3u 100BASE-T IEEE 802.3ab 1000BASE-T IEEE 802.3bz 2.5G/5GBase-T IEEE 802.3an 10G BASE-T IEEE 802.3z 1000BASE-SX/LX IEEE 802.3ae 10G Fiber IEEE 802.3x Full-Duplex Flow Control IEEE 802.1Q VLAN Tagging IEEE 802.1w RSTP IEEE 802.3ad LACP IEEE 802.1AB LLDP IEEE 802.3az Energy Efficient Ethernet (IEEE 802.1p Class of Service)
Form Factor	Desktop
LED Indicators	Per Port: Speed/Link/Activity Per System: Power/Status
Buttons	Reset button
Dimensions (HxWxD)	42.5 x 290 x 127 mm
Weight (Net)	1.15 kg
Weight (Gross)	1.75 kg
Operating Temperature	0°C to 40°C (32°F to 104°F)
Relative Humidity	5~95% Non-condensing
Certifications	CE, FCC, VCCI, BSMI
Electromagnetic Compliance	CLASS B
Jumbo Frames	9K
Warranty	2 Years

Note: Use only QNAP memory modules to maintain system performance and stability. For NAS devices with more than one memory slot, use QNAP modules with identical specifications.

Warning: Using unsupported modules may degrade performance, cause errors, or prevent the operating system from starting.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Product images are for illustrative purposes only and may differ from the actual product. Due to differences in monitors, colors of products may also appear different to those shown on the site.

Designs and specifications are subject to change without notice.