


Gun cabinet disassembly instructions




PARTS LIST



 A*1	 B*1	 C*1	 D*1	 H*1
				 I*1
				 J*1
 E*1	 F*1	 G*1	 K*1	 L*2
 S*4	 N*42	M*1	 O*2	
				

INSTRUCTIONS

STEP 1




N*10

Link Ⓐ,Ⓒ,Ⓓ with Self tapping threads.

Note:The bottom screws are not installed.


STEP 2



Sides and back, use screw links

N*10

STEP 3




Bottom and cabinet, use screws to link




N*6

STEP 4




Top and cabinet, use screws to link

STEP 5


S*4
G
Lift the divider when it's in place,
put pressure on the divider

STEP 6


0*2
F
The back of the gun stock holder. The bayonet on both sides is bent at 90 degrees
H
F
N*4

OPENING YOUR SAFE FOR THE FIRST TIME

Touch the keypad area, enter the password 1234, and press the "#" key to confirm. The speaker sounds "BI" long sound, then you can open the safe box (Factory password is 1234#)

PERSONAL PASSWORD SETTING

1. Press the setup button in the safe box .

2. When you hear a short “Di~,” the numeric keypad lights up. Enter a 1-8 digit password. Press the “#” key.

3. The speaker sounds "B-" and the indicator blinks. At this time, enter the password again and press the "#" key. The speaker sounds "BI--" for a long time, indicating that the password is successfully set.

FINGERPRINT SETTING

1. Press the setting key once, the buzzer beeps, the setting indicator, touch key light and fingerprint head light up

2. Place your finger on the fingerprint collector to collect fingerprints. Press the same finger five times to collect fingerprints.

3. The first three buzzers are accompanied by a beep, and the fifth buzzer beeps for a long time, indicating that the fingerprint registration is successful ; If the buzzer beeps, the configuration fails and you need to perform the operation again.

FOUR WAYS TO OPEN THE SAFE

1 . Emergency key + knob: For the first time, forget the password, and the battery is out of power. Insert the emergency key vertically, turn it to the left, and at the same time turn the knob to the right to open.

2. Password+ knob: Daily unlock. Enter the personal password or management password, press "#" , and then turn the knob to the right toopen .

3. Password+ knob + External power Box: The internal battery is dead, the key is damaged or lost. Insert the external power box, enter the personal password or management password, press "#" , and then turn the knob to the right to open.

4. fingerprint + knob: Enter your fingerprint and turn the knob to unlock.

VIBRATION ALARM

1. Touch the keypad area, and press the “*” key. All lights will turn on, and you will hear a long “Di~,” indicating that the alert is activated. When the safe is shaken by external forces, the horn will issue an alarm for 20s. Enter the correct password to deactivate the alarm.

2.Password verification failed for three consecutive times fingerprint verification failed for five consecutive times, the safe alarm sounded for 60 seconds,and the door was successfully opened to remove the alarm.

MUTE FUNCTION

Enter #00* to turn on silent mode, turn off the prompt tone except alarm sound, and enter #00* to turn off silent mode in silent mode.

RESTORE FACTORY SETTINGS

Long press the setting button for about 3 seconds (do not release),

and the speaker will sound "BI--" long.

LOW VOLTAGE

When the power supply voltage is lower than 4.8V, touch the wake up system, the three indicators blink 5 times at the same time, after the door is successfully opened, the right light blinks 5 times and beeps 5, please replace the battery as soon as possible