
Acropolis | E30232-122BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

A colonnade of faceted crystal columns form these rectangular wall sconces suitable for wet locations. The crystals are backlit with an evenly distributed LED light source that is set within non-corrosive Aluminum and Stainless Steel frames. With an extension compliant for ADA applications, this collection can be used on the interior or exterior of any space.



MEASUREMENTS

DIMENSION	: 8" W x 18" H x 3.25" Ext
BACK PLATE	: 7.75" W x 18" H x 9" HCO
HANGING WEIGHT	: 7.8 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,260 Rated (810 Del.)
BULB	: 1 x 18W LED AC Integrated , 18W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: All

FINISHES OPTION

Black (BK)

Natural Aged Brass (NAB)

GLASS

Clear Crystal 122

MATERIAL

Aluminum,Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 35000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com