



Howard Leight™ SmartFit®

Tapered Reusable TPE Corded Ear Plugs - NRR 25

- 25 dB NRR helps protect against moderate to high noise levels
- Conforming Material Technology™ uses body heat to adapt to the ear canal for a personalized fit
- Reusable triple-flange design provides consistent attenuation without rolling
- Soft TPE material offers long-lasting comfort and durability
- One-size-fits-most design simplifies inventory and improves compliance
- Push-in insertion ideal for dirty or gloved work environments
- Attached cotton cord reduces loss and allows convenient intermittent use
- High-visibility orange color for easy compliance checks
- Meets ANSI and OSHA hearing protection standards

Technical Data

Color	Orange
Sizes Available	OS
Packaging	Bulk Boxed
Packed	500 Pair/Case
Case Weight (lbs)	0.00
Country of Origin	Mexico
Hearing Style	Corded
Ear Plug Material	Thermoplastic Elastomer
Shape	Tapered
Cord Material	Vinyl
Box Count	500
Certifications	TAA Compliant
Product Circularity	Reusable / Launderable

Performance Data

NRR Rating (ANSI S3.19-1974)	25
SLC 80 Class	Class

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-17

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
SMF-30W-P	Orange	OS	033552013488		