



Technical Data

Color	Dark Blue, Black, Red, Yellow, White, Gray, Orange, Green
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	23.00 x 19.00 x 23.00
Case Weight (lbs)	22.99
Country of Origin	Mexico
Shell	Non-Vented
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Fibre-Metal® Roughneck™ P2

Type I, Non-Vented, Cap-Style Smooth Dome
Hard Hat with High Heat Resistant Proprietary
Fiberglass Shell, 8-Point SuperEight™ Suspension
and Wheel Ratchet Adjustment

- Best-in-class high heat resistance meets ANSI-Z89.1-2009 impact tests at extreme temperatures of up to 500°F
- Proprietary heat resistant fiberglass compound offers exceptional impact resistance, and is eight times stronger than common High-Density Polyethylene (HDPE)
- The advanced SuperEight™ suspension balances and spreads weight over a wide area for added comfort and impact protection
- Solid color resin provides a permanent, no-chip, no-peel finish
- Smooth, matte finish makes logo imprints crisper and cleaner, so your official company hard hats look better and last longer
- Meets ANSI/ISEA Z89.1, Type I, Class E requirements

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
P2HNRW11A000	Black	OS	821812541792		00821812541846
P2HNRW71A000	Dark Blue	OS	821812391342		00821812391359
P2HNRW09A000	Gray	OS	821812541778		00821812541822
P2HNRW74A000	Green	OS	821812378565		00821812378572
P2HNRW03A000	Orange	OS	821812401782		00821812401799
P2HNRW15A000	Red	OS	821812378602		00821812378619
P2HNRW01A000	White	OS	821812378541		00821812378558
P2HNRW02A000	Yellow	OS	821812378589		00821812378596