Rampart | E30114-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Sharp rectilinear metal lines surround a squared LED housing that shines both upwards and downwards, creating an intriguing pattern of light. This collection offers a full range of products that suits exterior and interiors without bounds. Available in a variety of sconce sizes, as well as an additional pendant and post mount option, the design is completed in a matte Black finish that complements most settings.



MEASUREMENTS

DIMENSION	: 5.5" W x 11.75" H x 2.5" Ext
BACK PLATE	: 4.5" W x 4.5" H x 6" HCO
HANGING WEIGHT	: 2.2 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 840 Rated (600 Del.)
BULB	: 2 x 6W LED PCB Integrated , 12W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Up/Down

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com