



### Technical Data



### Bouton® Optical Commander™

Semi-Rimless Safety Glasses with Gloss Bronze Frame, Clear Lens and Anti-Scratch / Anti-Fog Coating

- Lightweight, semi-rimless design offers extensive eye coverage and all day comfort
- Bayonet style temples with non-slip rubber pads provide a secure fit
- Adjustable rubber nose pads offer a custom, comfortable fit
- 9.5 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

|                      |                                                   |
|----------------------|---------------------------------------------------|
| Color                | Bronze                                            |
| Sizes Available      | OS                                                |
| Packaging            | Bagged Each                                       |
| Packed               | 144 Pair/Case                                     |
| Case Dimensions (in) | 23.62 x 14.76 x 16.73                             |
| Case Weight (lbs)    | 16.09                                             |
| Country of Origin    | Taiwan                                            |
| Lens                 | Clear                                             |
| Frame Style          | Semi-Rimless                                      |
| Lens Color           | Clear                                             |
| Frame Fit            | Universal                                         |
| Lens Coating         | Anti-Scratch, Anti-Fog                            |
| Bridge               | Rubber                                            |
| Temple               | Bayonet                                           |
| Base Curve           | 9.5                                               |
| Certifications       | ANSI Z87.1, TAA Compliant, EN 166, EN 170, EN 172 |

### Applications

- General Manufacturing
- Construction Applications
- Indoor Work

## SKU Information

| SKU         | FRAME COLOR | LENS                | LENS COLOR | LENS    | UPC          | UPC (INNER)    | UPC (CASE)     |
|-------------|-------------|---------------------|------------|---------|--------------|----------------|----------------|
|             |             |                     |            | COATING |              |                |                |
| 250-33-0010 | Black       | Clear               | Clear      | AS/AR   | 616314130342 | 01616314130341 | 02616314130340 |
| 250-33-0020 | Black       | Clear               | Clear      | AS/AF   | 616314130328 | 01616314130327 | 02616314130326 |
| 250-33-0021 | Black       | Tinted              | Gray       | AS/AF   | 616314130335 | 01616314130334 | 02616314130333 |
| 250-33-0041 | Black       | Polarized           | Gray       | AS      | 616314130366 | 01616314130365 | 02616314130364 |
| 250-33-0226 | Black       | Indoor Outdoor Blue | Clear      | AS/AF   | 616314130359 | 01616314130358 | 02616314130357 |
| 250-33-1010 | Bronze      | Clear               | Clear      | AS/AR   | 616314130397 | 01616314130396 | 02616314130395 |
| 250-33-1020 | Bronze      | Clear               | Clear      | AS/AF   | 616314130373 | 01616314130372 | 02616314130371 |
| 250-33-1024 | Bronze      | Tinted              | Gray       | AS/AF   | 616314130380 | 01616314130389 | 02616314130388 |
| 250-33-1226 | Bronze      | Indoor Outdoor Blue | Clear      | AS/AF   | 616314130403 | 01616314130402 | 02616314130401 |

**KEY:** AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated