

CORTINA

550-72-VB

Inspired by a modern mobile, Cortina's linear bars dangle from a complex marionette suspension. Beneath the Vintage Brass-finished frame, cast piastre glass with a subtle optic texture adds interest to the streamlined fixture. As a 3-light chandelier, Cortina can serve as a piece of functional art in a grand entryway. The single island light is perfect above a kitchen counter.

FINISHES

VINTAGE BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 22"

Width/Diameter: 72"

Minimum Height: 15.75"

Maximum Height: 96.25"

Canopy/Backplate: 17.75"

Hanging Type: 72" Chain

Product Weight: 21lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: Yes

Uplight Only: No

Shade

Shade 1: Cast Glass

Shade 1 Finish: Piastre

Shade 1 Top Length: 8.25"

Shade 1 Height: 0.75"



ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 56

Bulb Quantity: 3

Wire Length: 144"

Cord Type: LOW VOLTAGE DC WIRE

Dimmer Type: TRIAC, 0-10 VOLT

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 1575

Title 24: No

Field Serviceable: No

SHIPPING

Carton 1: 78" x 22" x 8"

Carton 1 Weight: 26lb

Shipping Method: Truck Only

Country of Origin: VN