

ELIAS

F3638-FOR

The Elias chandelier brings organic texture to a bold architectural frame. A large woven Saguran drum shade lends warmth, while slender Forged Iron arms introduce graphic clarity. The light source is housed within a simple bowl, replacing a traditional candle cluster with a clean, modern silhouette. Available with 4 or 6 lights, it makes an approachable, yet substantive impression.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

FORGED IRON

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 30.75"

Width/Diameter: 38"

Minimum Height: 37.75"

Maximum Height: 104"

Canopy/Backplate: 5"

Hanging Type: 72" Chain

Product Weight: 24.2lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Saguran

Shade 1 Top Width: 38"

Shade 1 Bottom L/W: 0" / 38"

Shade 1 Height: 14.25"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 6

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 43" x 43" x 34"

Carton 1 Weight: 44lb

Shipping Method: Truck Only

Country of Origin: PH

