Project / Job Name:

Location:

Fixture Type:

Notes:



67-580 - Emergency Light; 120-347V; 2HR Backup; Universal Mounting; Wet Location; White Finish

GENERAL

Company	SATCO
EA Height	10.43
EA Width	2.83
EA Length	12.48
Bulb Included	Integrated
Material	Thermo Plastic
Fixture Type	Emergency Light
Product Notes	Ni-Cad Battery; 120 minute discharge time; 24 Hour Recharge Time
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	120%-140%
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Amps	0.029-0.010A
Has Camera	No
IOT Enabled	No
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Power Factor	0.45
SDS Class	LED_Fixture
Sloped Ceiling Compatible	No
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	5000K
Dimmable	Non-Dimmable
Color Temp	Natural Light
CRI	80+
Operating Frequency	50/60Hz
Operating Temp	+32F to +122F (0C to +50C)
Lumens	600L
Volts	120V-347V
Watts	3.5W
Battery Chemistry	Ni-Cad

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Universal

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923675973
Case Cube	1.4971
Case Height	13.19
Case Length	18.11
Case Quantity	6
Case UPC	10045923675970
Case Weight	19.62
Case Width	10.83
EA Cube	0.2132
EA Height	10.43
EA Length	12.48
EA Quantity	1
EA Weight	2.65
EA Width	2.83
Pack Type	Box
Web Height	11.56
Web Width	10.2

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	CSAus
California Ban	Non-Compliant
Title 20	No
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026