Pilar | E14370-GSN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

This outdoor collection is cast in concrete for maximum durability in harsh climates such as coastal environments. Available in your choice of a lighter Sandstone or darker Greystone Aggregate, both are powered by dual integrated LED boards for efficient and long-life operation.



MEASUREMENTS

DIMENSION	: 4.5" L x 4.5" W x 7" H
CANOPY	: 3.93" W x 3.93" H x 0.59" L
HANGING WEIGHT	: 2.45 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 700 Rated (600 Del.)
BULB	: 1 x 7W LED E26 Medium , 7W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Greystone (GSN)

Sandstone (SSN)

MATERIAL

Concrete, Steel

RATINGS

cETLus
Damp Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com