

SONNY

B2828-BRL

Sonny takes inspiration from a mid-century sputnik chandelier, reimagined with an organic, staggered rhythm. Finished in Bronze Leaf, slender arms extend outward, culminating in a softly glowing cloud seedy glass globe. The seemingly randomized arrangement creates a dynamic, almost celestial composition. Available as a 4-light sconce and a 12- or 20-light chandelier, Sonny serves as a stunning centerpiece for dining or living spaces.

FINISHES

BRONZE LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 28"

Width/Diameter: 10.25"

Canopy/Backplate: 4.75"

Product Weight: 6.6lb

Extension: 7.5"

Top to Center: 14"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Seeded Cloud

Shade 1 Top Width: 5.5"

Shade 1 Height: 5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 4

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 32" x 10" x 12"

Carton 1 Weight: 11lb

Shipping Method: Ground

Country of Origin: PH

