

KATYA

HL1089401-AGB

Statuesque and expressive, the Katya floor lamp adds graphic elements to an elongated form. Three curved legs with delicate ball feet support a slender stem, creating a silhouette that draws from both a traditional and modern design lexicon. Topped with a conical cotton shade, Katya casts a soft, flattering light that reflects off the Aged Brass finish.

FINISHES

AGED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 61"

Width/Diameter: 25.5"

Canopy/Backplate: 21.25"

Product Weight: 14lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: Cotton

Shade 1 Top Width: 25.5"

Shade 1 Height: 10.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 96"

Cord Type: SPT-2 TAUPE FABRIC

Switch Type: ON/OFF STOMP SWITCH

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 38" x 27" x 25"

Carton 1 Weight: 27lb

Shipping Method: Truck Only

Country of Origin: VN

