
ASSEMBLY AND INSTALLATION INSTRUCTIONS


P0480 / C0389 / P0481 / C0390 / P0482 / C0391 /
P0483 / C0392 / P0484 / C0393 / P0485 / C0394


WARNING: TO AVOID RISK OF ELECTRICAL SHOCK, BE SURE TO SHUT OFF POWER WHILE INSTALLING OR SERVICING THIS FIXTURE.

NOTE: 1. Before installing, consult local electrical codes for wiring and grounding requirements.
2. Read and save these instructions.

Hardware Package (included):



Mounting Plate Unit (A)


Mounting Screw (B)


Wire Connector (C)


Bolt Nut (D)


Strain Relief (E)



Installation Steps for Pendant:

Turn off the power at fuse or circuit box

1. Unscrew the two bolt nuts (D), remove the mounting plate unit (A) from the canopy.

2. Thread the cable through the canopy and two holes of the strain relief (E).

3. Release the cable to desired length by adjusting the strain relief (E).

4. Attach mounting plate unit (A) to the outlet box using two mounting screws (B). Adjust the length of the preinstalled fixture mounting screws if necessary.


5. Pull out the source wires from the outlet box. Make wire connections wire connectors (C) as follows:
   -- Connect the fixture black wire to the house black wire using wire connector (C) provided.
   -- Connect the fixture white wire to the house white wire using wire connector (C) provided.
   -- Connect the bare ground wire from the canopy to the mounting plate unit (A) by securing it with the preinstalled green ground screw, then connect it to the fixture green ground wire and the house ground wire with wire connector (C).
   Tuck all the wires into outlet box.

6. Secure the canopy to the mounting plate unit (A) by inserting the fixture mounting screws, then secure it with two bolt nuts (D).

7. Attach the metal shade to the socket, then secure it with the socket ring.
   Install 1 x 60W Max. medium base bulb (not included).
   See relamping label at socket area or packaging for maximum wattage allowed.

VAXCEL
260714


8. Angled mounting recommended for a vaulted or angled ceiling (See Fig.A).



Turn on the power at fuse or circuit box

Installation Steps for Semi-Flush Mount:

Turn off the power at fuse or circuit box



1. Unscrew the two bolt nuts (D), remove the mounting plate unit (A) from the canopy (A).


2. Attach the mounting plate unit (H) to the outlet box by using two mounting screws (B).


3. Remove the stem and threaded pipe from the canopy by disassemblying the hex nut, ground wire tab, washer and pad (See Fig. 1).


4. Thread fixture wire through threaded pipe, canopy, pad, washer, ground wire tab and hex nut, rotate the threaded pipe into the fixture, secure the canopy on the the threaded pipe by using pad, washer, ground wire tab and hex nut (See Fig. 2).

5. Leave an additional 9" of cable (a) above the canopy (include the canopy), and then cut off the unnecessary cable.
   Mark the 3" of cable (b) from the top of the cable (a). Use a knife to peel off the insulation of the cable (b) carefully to expose three internal wires.
   Note: Cutting too deep may cut off the internal wires and destroy the insulation surface of the internal wires.
   Peel off the wires from the top about 3/8" long (c) to expose the copper for wiring (See Fig. 3).

6. Pull out the source wires from the outlet box.
   Make wire connections using wire connectors (C) as follows:
   -- Connect the fixture black wire to the house black wire using wire connector (C) provided.
   -- Connect the fixture white wire to the house white wire using wire connector (C) provided.
   -- Connect the bare ground wire from the canopy to the mounting plate unit (A) by securing it with the preinstalled green ground screw, then connect it to the fixture green ground wire and the house ground wire with wire connector (C).
   Tuck all the wires into outlet box.







7. Attach the canopy to the mounting plate unit (A) by inserting the fixture mounting screws, then secure it with two bolt nuts (D).

8. Attach the metal shade to the socket, then secure it with the socket ring.


9. Install 1 x 60W Max. medium base bulb (not included).
   See relamping label at socket area or packaging for maximum wattage allowed.


Turn on the power at fuse or circuit box

VAXCEL
260714

The following parts are available for reorder if damaged or missing.


Spare Parts List:





A: 7" **C: 8"**

B: 12-3/4" **D: 12-3/4"**



1 Year Warranty

Vaxcel warrants all of our products against defects in workmanship and finishes for one year following the date of shipment.

Exclusions: This warranty does not include the failure of products from extreme acts of nature; environmental conditions not suited for the products intended use; operation in temperatures outside of the range specified in the instruction manual; usage with improper power supply, power surges or dips. For coastal locations, some corrosion is considered normal for the environment.

Vaxcel reserves the right to repair, replace or issue a credit for any properly installed product, provided it is returned per RMA instruction. This warranty is limited to the cost of the product only and does not extend to transportation, installation or replacement costs.

How can warranty service be obtained?
info@vaxcel.com
1-800-482-9235

VAXCEL
260714