Bombona | E20256-142BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Large cylindrical glass shades feature a unique return as they are illuminated with LED integrated light sources. Available in 3 varying proportions, a combination of which adds a moody, contemporary styling to your interior space.



MEASUREMENTS

DIMENSION	: 12" W x 16" H
MAX OAH	: 61.5" OAH
CANOPY	: 4.75" W x 0.75" H x 4.75" L
HANGING WEIGHT	: 7.98 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,810 Rated (990 Del.)
BULB	: 1 x 22W LED AC Integrated , 22W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

GLASS

Graduating Smoke 142

MATERIAL

Steel, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 90
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com