



North®

Short Brim, Type I Vented, Hard Hat with HDPE Shell, 4-Point Textile Suspension, Wheel Ratchet Adjustment and Optional 4-Point Chinstrap

- 4-Point textile suspension, with ratchet adjustment
- Dual-locking mechanism prevents the hard hat from coming loose
- Optional four-point chin strap available
- Lightweight yet durable HDPE shell
- Vented option provides increased airflow to help workers stay cool

Technical Data

Color	Gray, White, Red, Green, Dark Blue, Orange, Black, Yellow
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	22.44 x 17.72 x 18.50
Case Weight (lbs)	21.38
Country of Origin	China
Shell Material	HDPE
Shell	Non-Vented
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Certifications	ANSI/ISEA Z89.1, EN 397, CSA Z94.1 Certified

Performance Data

ANSI Type	Type I
-----------	--------

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
NSB21011	Black	OS	883940433080		00883940433240
NSB21071	Dark Blue	OS	883940433103		00883940433264
NSB21009	Gray	OS	883940433073		00883940433233
NSB21004	Green	OS	883940433066		00883940433226
NSB21003	Orange	OS	883940433059		00883940433219
NSB21015	Red	OS	883940433097		00883940433257
NSB21001	White	OS	883940433035		00883940433196
NSB21002	Yellow	OS	883940433042		00883940433202