

JARVIS

PTL4524-PBR/CDL

The eye-catching, teardrop base of the Jarvis lamp recalls a hand-shaped vase. Creating an organic surface texture with a fluid finish, the Dappled Lapis ceramic glaze has a subtly reflective quality. Finished with self-trim, an off-white linen shade plays with proportion to add interest to the silhouette. Accented by Patina Brass hardware, Jarvis adds a pop of color to nightstands, consoles, and side tables.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

PATINA BRASS w/ Ceramic Dappled Lapis
Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 24"
Width/Diameter: 15.5"
Canopy/Backplate: 3.75"
Product Weight: 8lb
Canopy/Backplate Shape: Oval
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Textile
Shade 1 Finish: White Linen
Shade 1 Top Width: 10"
Shade 1 Bottom L/W: 0" / 15.5"
Shade 1 Height: 13.75"

ELECTRICAL



Bulb 1

Bulb Included: No
Socket: E26 Medium Base
Bulb Type: A19
Max Wattage: 15
Bulb Quantity: 1
Wire Length: 96"
Cord Type: SPT-2 BLACK FABRIC
Switch Type: ON/OFF SWITCH ON SOCKET
Gem Box Required (2"x3"): No
Dark Sky: No

SHIPPING

Carton 1: 18" x 18" x 27"
Carton 1 Weight: 16lb
Shipping Method: Ground
Country of Origin: VN

