Blossom | E32795-93NAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A branched frame inspired by a close observation of nature. Finely engineered and designed in delicate detail, the soft Gold finish pairs with organically formed Morning Frost glass that is partially frosted to conceal the LED light source within. Contemporary in design and soft in nature, this collection complements both modern and transitional aesthetics.



*max overall height

MEASUREMENTS

DIMENSION	: 43.25" L x 35.75" W x 25.75" H
MAX OAH	: 72.75" OAH
CANOPY	: 5.25" W x 1" H x 5.25" L
HANGING WEIGHT	: 9.9 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,500 Rated (2,000 Del.)
BULB	: 5 x 4W LED G9 , 20W Total
BULB INCLUDED	: (Included)
DIMMABLE	: ELV or Triac
CRI	: 80 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Natural Aged Brass (NAB)

GLASS

Clear and Frosted 93

MATERIAL

Steel, Aluminum

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 30
RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com