



G-Tek® PosiGrip MAX™

Seamless Knit PolyKor® Blended Glove with PosiGrip MAX™ Coating on Palm & Fingers - Touchscreen

- Seamless construction offers increased comfort and breathability
- Premium PolyKor® blended 18G shell is lightweight and provides excellent dexterity, tactile sensitivity, and cut resistance
- Proprietary PosiGrip MAX™ is a bi-polymer coating that has the best properties of both nitrile and polyurethane
- This unique coating reduces required gripping force by up to 35% in dry/ oily conditions and provides enhanced tactility for handling small parts
- PosiGrip MAX™ coating boasts near 0% oil penetration for safer skin and a reduced rate of glove changeouts from oil exposure
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves
- ⚠ **WARNING:** Cancer - www.P65Warnings.ca.gov



Technical Data

Color	Black
Sizes Available	XS-3XL
Packaging	Bulk Pack
Packed	6 Dozen/Case
Case Dimensions (in)	14.57 x 11.42 x 7.09
Case Weight (lbs)	7.28
Country of Origin	China
Liner Material	PolyKor
Coating	PosiGrip Max
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Flat
Gauge	18
Cuff	Knit Wrist
Construction	Coated Seamless Knit, Touchscreen Compatible, Reinforced Thumb Crotch
Certifications	Latex Free

Performance Data

Cut Level	A4
ANSI Abrasion Level	3
ANSI Puncture Level	3
EN 388	4X42D
EN 407	X1XXXX

Care Instructions



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
16-848/XS	Black	XS	198987000806	10198987000803	20198987000800
16-848/S	Black	S	198987000844	10198987000841	20198987000848
16-848/M	Black	M	198987000882	10198987000889	20198987000886
16-848/L	Black	L	198987000929	10198987000926	20198987000923
16-848/XL	Black	XL	198987000967	10198987000964	20198987000961
16-848/XXL	Black	2XL	198987001001	10198987001008	20198987001005
16-848/XXXL	Black	3XL	198987001049	10198987001046	20198987001043