

BEATA

HL1117201-AGB/CHC

The Beata table lamp makes a sculptural, yet playful statement. A rounded ceramic base, finished in a Harbor Gray Crackle glaze, recalls the shape of a pumpkin. The elongated white linen shade balances the voluminous form, while Aged Brass hardware at the neck adds a polished note. Both charming and grounded, this lamp adds instant personality to a room.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

AGED BRASS w/ Ceramic Harbour Grey Cackle
Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 21"
Width/Diameter: 17"
Canopy/Backplate: 3.75"
Product Weight: 9lb
Canopy/Backplate Shape: Round
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Textile
Shade 1 Finish: White Linen
Shade 1 Top Width: 13"
Shade 1 Bottom L/W: 0" / 17"
Shade 1 Height: 11"

ELECTRICAL



Bulb 1

Bulb Included: No
Socket: E26 Medium Base
Bulb Type: A19
Max Wattage: 15
Bulb Quantity: 1
Wire Length: 96"
Cord Type: SPT-2 BLACK FABRIC
Switch Type: ON/OFF SWITCH ON SOCKET
Gem Box Required (2"x3"): No
Dark Sky: No

SHIPPING

Carton 1: 16" x 16" x 26"
Carton 1 Weight: 17lb
Shipping Method: Ground
Country of Origin: VN

