

STONEY

F2540-PBR

The architectural design language of the Stoney family is softened by its unique material qualities. Large conical white linen shades are edged with contrasting whip-stitching, echoing the natural jute wrap details along the Patina Brass frames. Available as a 1-light sconce, 1-light pendant, 5-light chandelier, and 1-light floor lamp, Stoney is an ode to craftsmanship.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 15.75"

Width/Diameter: 40.25"

Minimum Height: 22.5"

Maximum Height: 63.75"

Canopy/Backplate: 5.5"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 16lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: White Linen

Shade 1 Top Width: 2.25"

Shade 1 Bottom L/W: 0" / 10.25"

Shade 1 Height: 7"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 5

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 36" x 35" x 16"

Carton 1 Weight: 27lb

Shipping Method: Truck Only

Country of Origin: VN

