




TEGERA® WELDING 19

Learn more

PROTECTS AGAINST HOT OBJECTS

Long-lasting performance and high anti-burn protection, for welding jobs. All day comfort thanks to the flexible split cowhide. Cotton jersey liner inside the glove for better sweat management. Reinforced seams for extra durability. Elasticated wrist for better fit.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Very durable
- Good fit

FUNCTIONS

- Withstands contact heat up to 100°C
- Reinforced seams
- Flame retardant
- Withstands welding sparks and grinding splash

LEATHER WORKING GROUP

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Burn injuries, Heat injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations

PRIMARY ENVIRONMENTS OF USE

Warm environments, Harsh environments

PRIMARY AREAS OF USE

Engineering, Hot work, Mining, Welding

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Mining and quarrying

TYPE OF WORK

Heavy weight

SPECIFICATION

TYPE Heat protection gloves, Welding gloves
CATEGORY Cat. III
COLLECTION Welding
PALM MATERIAL Split cowhide of top quality
BACK MATERIAL Split cowhide of top quality
LINING Fully lined
LINING MATERIAL Jersey
LENGTH 320-365 mm
DEXTERITY 1
COLOUR Yellow
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE No thread
FASTENING Elasticated 180°
CUFF STYLE Extended safety cuff
CUFF MATERIAL Leather
INNER MATERIAL SPECIFICATION Cotton, Polyester
OUTER MATERIAL SPECIFICATION Leather

COMPLIANCE

CE 2777

UKCA 0321

EAC

TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018
2144X

EN 407:2020
(Welding)
41334X

EN 12477:2001+A1:2005

Type A

EN 1149-2:1997
R > 1,0 x 10^5 Ω

ANSI 4 ABR

SIZE		ARTICLE NUMBER	EAN
7	S	19-7	7333506034815
8	M	19-8	7392626072299
9	L	19-9	7340118300948
10	XL	19-10	7392626001992
11	XXL	19-11	7392626027473

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.