



PIP® Stromboli™

Type II, Cap Style Smooth Dome Hard Hat with Heat Resistant ABS/Polycarbonate Shell, 4-Point Textile Suspension and Wheel Ratchet Adjustment

- Lightweight shell made with UV stabilized ABS/Polycarbonate shell reduces worker fatigue
- Smooth dome styling is popular in construction, welding and metal working
- The smooth dome makes it ideal for use with welding helmets and the PC/ABS construction helps with protection from sparks, can be reverse donned
- Meets -ANSI/ISEA Z89.1 Type II and CSA Z94.1 Type II requirements
- EPS Liner for enhanced side, front and rear impact protection
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit

Applications

- Mining
- Tunneling
- Demolition
- Utility Work
- Metalworking

Technical Data

Color	Forest Green, Black, Red, Dark Green, Gray, White, Yellow, Orange, Steel Blue, Lime
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	20.30 x 14.00 x 28.10
Case Weight (lbs)	11.46
Country of Origin	Canada
Shell Material	ABS / Polycarbonate
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type II
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP842R-11	Black	OS	620606003023	10616314300650	10620606003020
280-HP842R-04	Dark Green	OS	620606003719	10616314300698	10620606003716
280-HP842R-74	Forest Green	OS	620606003054	10616314300704	10620606003051
280-HP842R-09	Gray	OS	620606003016	10616314300698	10620606003013
280-HP842R-45	Lime	OS	620606004259	10616314300810	10620606004256
280-HP842R-03	Orange	OS	620606003009	10616314300810	10620606003006
280-HP842R-15	Red	OS	620606003030	10616314300858	10620606003037
280-HP842R-71	Steel Blue	OS	620606003047	10616314300872	10620606003044
280-HP842R-01	White	OS	620606002989	10616314300933	10620606002986
280-HP842R-02	Yellow	OS	620606002996	10620606002993	10620606002993