
# **Canello** | E30092-01BK


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







## PRODUCT DESCRIPTION




**MEASUREMENTS**

| | |
|---|---|
| DIMENSION | : 24.5" L x 4.5" W x 24.5" H x 4" Ext |
| BACK PLATE | : 4.5" W x 4.5" H x 12.25" HCO |
| HANGING WEIGHT | : 2.1 lb |

**LAMPING**

| | |
|---|---|
| INPUT VOLTAGE | : 120-277V |
| LUMENS | : 1,120 Rated (1,090 Del.) |
| BULB | : 1 x 14W LED DC Integrated , 14W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : Triac or ELV at 120V |
| CRI | : 90 CRI |
| COLOR_TEMP | : 3000K |
| LIGHTING_DIRECTION | : Any |

**FINISHES OPTION**

Black (BK)

**GLASS**

White 01

**MATERIAL**

Aluminum, PC

**RATINGS**

cETLus
Wet Location
ADA

**ADDITIONAL**

INSTALL UP/DOWN: Any
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com