Cortex | E11062-144NAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A central, cylinder diffuser of opal white acrylic diffuses LED lighting within a cavity of thin ribbed glass of various lengths. Both imaginative and functional, the bright pendants encase an additional down light recessed within a Polished Chrome, Naturally Aged Brass or Matte Black housing casting light downward.



*max overall height

MEASUREMENTS

DIMENSION	: 1.5" L x 1.5" W x 14.5" H
MAX OAH	: 137.25" OAH
CANOPY	: 4.75" W x 1.75" H x 4.75" L
HANGING WEIGHT	: 2.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 800 Rated (600 Del.)
BULB	: 1 x 10W LED PCB Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Black (BK)
- Natural Aged Brass (NAB)
- Polished Chrome (PC)

GLASS

Clear Ribbed 144

MATERIAL

Steel, Aluminum, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com