



Technical Data

Color	Black
Sizes Available	OS
Packaging	Bagged Pair
Packed	200/Case
Case Weight (lbs)	0.00
Country of Origin	Taiwan
Lens	Clear
Frame Style	Semi-Rimless
Lens Color	Clear
Lens Coating	Anti-Scratch,
Bridge	Rubber
Diopter	1.50
Certifications	CSA Z94.3 Certified, TAA Compliant

UVEX® A900

Semi-Rimless Readers with Black Frame, Clear Lens and Anti-Scratch, Hard Coating - +1.50 Diopter

- Sporty, 8 Base wrap-around polycarbonate lens
- Non-slip rubber nose bridge
- Temples with soft, padded inserts provide a comfortable fit
- Provides 99.9% UV protection
- +1.5 Diopter
- Meets ANSI Z87.1+
- Meets CSA Z94.3

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
A950	Black	Clear	Clear	AS/	040025000821		

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated