

Project Name

Location

Prepared By



Notes

[www] 08-09-2023 03:33:00

General

Status	Active
Collection	Glamour
Finish	Brushed Nickel
Wattage	50W
Style	Contemporary
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm White to Natural Light
Width (in.)	48.98
Height (in.)	5.71
Extension (in.)	2.83
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
Integrated Camera	No

Specifications

Technology	LED
CRI	90+
Lumen Output	3371L/3494L/3819L/3937L/3968L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	4.45
Fixture Material	Steel
Fixture Type	Vanity
Operating Temperature	-20C (-4F) to +40C (+104F)

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
ADA Compliant	Yes
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5-Years
----------	---------