



## jalas® HEAVY DUTY 1378

ASTM F2413-18 M/I/C/SD 35/PR  EN ISO 20345:2011 S3, SRC, CI, HRO

Learn more

## THE ULTIMATE WINTER SAFETY BOOT FOR HARSH CONDITIONS

A fully lined winter safety boot with highest (S3) protection designed for very cold or slippery conditions. The PU-coated leather, and synthetic fur and Thinsulate™ lining mean feet are protected in any conditions. The oil and heat-resistant Vibram Arctic Grip sole provides outstanding grip, and JALAS® Composite Toe Cap, steel puncture protection and double impact protection zones in PORON® XRD®. Comes with blue and black laces.

### CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Extremely warm
- Excellent shock absorption
- Light

### FUNCTIONS

- ProNose toe reinforcement
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Extra shoelaces
- Ankle support
- Pull loops
- Snow lock
- Arctic Grip traction outsole
- Zipper
- Antistatic/ATEX
- Water repellent
- Reflector
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*

## PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic, Contact with cold, Slipping

## PRIMARY ENVIRONMENTS OF USE

Outdoors, Slippery environments, Cold environments, Harsh environments

## SPECIFICATION

**TYPE** Safety footwear, Boots/Ankle boots
**CATEGORY** Cat. II
**NAIL PROTECTION MATERIAL** Steel
**FITTING** Regular
**COLLECTION** Heavy Duty
**UPPER MATERIAL** PU-coated leather
**PRONOSE MATERIAL** PU
**TOECAP MATERIAL** Composite
**LINING MATERIAL** Polyester fur, Thinsulate™
**INSOLE** JALAS 8245 FX2 ThermAL
**INNERSOLE MATERIAL** Textile, Aluminium foil, Soft EVA, Polyester-based conductive thread, Merino wool, Double shock absorption zones in PORON® XRD®
**MIDSOLE MATERIAL** PU midsole
**OUTSOLE MATERIAL** Arctic Grip traction outsole (HNBR rubber + gripper lugs)
**FASTENING** Laces, Zipper
**SHOELACES LENGTH** 160 cm
**COLOUR** Black
**NET WEIGHT, (SIZE 42)** 1.74 kg

## COMPLIANCE

CE Cat. II

ASTM F2413-18
M/I/C/SD 35/PR

EAC TP TC 019:2011

EN ISO 20345:2011
S3, SRC, CI, HRO

## FEATURES

- Anti-static properties
- Composite toecap
- Ergothan Shock Absorption System
- ESD
- Oil-resistant outsole
- ProNose toe reinforcement
- Nail protection in steel
- Heat-resistant outsole
- Water repellent
- Winter model
- Zipper

| SIZE | | | | ARTICLE NUMBER | EAN |
|---|---|---|---|---|---|
| EU | UK | US M | US W | | |
| 35 | 2 | 3.5 | 4 | 1378-35 | 6408487506222 |
| 36 | 3 | 4 | 5 | 1378-36 | 6408487506239 |
| 37 | 4 | 5 | 6 | 1378-37 | 6408487506246 |
| 38 | 5 | 5.5 | 6.5 | 1378-38 | 6408487506253 |
| 39 | 6 | 6.5 | 7.5 | 1378-39 | 6408487506260 |
| 40 | 6.5 | 7.5 | 8.5 | 1378-40 | 6408487506277 |
| 41 | 7 | 8 | 9 | 1378-41 | 6408487506284 |
| 42 | 8 | 9 | 10 | 1378-42 | 6408487506291 |
| 43 | 9 | 9.5 | 11 | 1378-43 | 6408487506307 |
| 44 | 10 | 10.5 | 11.5 | 1378-44 | 6408487506314 |
| 47 | 12 | 13 | 14 | 1378-47 | 6408487506345 |
| 48 | 13 | 13.5 | 14.5 | 1378-48 | 6408487506352 |

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*