



Technical Data

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	26.30 x 10.91 x 11.38
Case Weight (lbs)	17.64
Country of Origin	Malaysia
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Rubber
Temple	Adjustable Length, Spatula
Base Curve	8
Certifications	ANSI Z87.1, CSA Z94.3 Compliant
Product Circularity	Recycled via Terracycle

Wilco™

Rimless Safety Glasses with Black Temple, Clear Lens and Anti-Scratch Coating

- Lightweight, rimless design provides all day user comfort
- Adjustable length temples provide a secure, accurate fit
- Ribbed rubber nosepiece for maximum comfort and fit
- 7 Base curve lens
- Meets ANSI Z87.1+
- Meets CSA Z94.3
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-92-0000	Black	Clear	Clear	AS	616314131462	01616314131461	02616314131460
250-92-0001	Black	Tinted	Gray	AS	616314131479	01616314131478	02616314131477
250-92-0002	Black	I/O	Clear	AS	616314131486	01616314131485	02616314131484
250-92-0005	Black	Mirror	Silver	AS	616314161940	01616314161949	02616314161948
250-92-0009	Black	Tinted	Amber	AS	616314131493	01616314131492	02616314131491
250-92-0020	Black	Clear	Clear	AS/AF	616314131509	01616314131508	02616314131507
250-92-0021	Black	Tinted	Gray	AS/AF	616314161957	01616314161956	02616314161955

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated