
TELESCOPIC LADDER

Instructions Manual





CONTENTS

English ---------- 01-03

日本語 ---------- 04-06











Preface



How to use:

Extending the ladder

Place it on the level ground and stretch it to the level you want. Please check that all the buttons on the position are totally locked.
(Tips: when the button lock, you'll hear a crisp "click")



Retracting the Ladder

Unlock steps from the bottom step one by one to retract the ladder.



As picture shows, before we unlock the step, put the hand on the outside of the ladder first.



Catch the ladder with one hand and slide the black lock button to unlock the step with another hand.




After we unlock the step, pull down the ladder to retract.




The other steps are all retracted in the same way, and finally fix the ladder with belt.

Be careful, put your hand between steps when retracting the ladder will pinch your finger.



Closing the ladder



Closing the ladder

Note:

In case of switch falling by acclident, there are a palr of replacement switches included in the packageJust insert it to the hole and you can use the ladder.

Using the ladder

1. Do not exceed the maximum total load (330lbs).
2. Do not overreach. Users keep both feet on the same step throughout the task.
3. Do not step off a leaning ladder of access to another level.
4. Do not stand on the top three steps of a leaning ladder.
5. Ladders should only be used for light work of short duration.
6. Do not use the ladder outside in adverse weather condition.
7. Take precautions against children playing on the ladder.
8. Face the ladder when going up and down.
9. Place the ladder on a firm level surface. Do not place on a unstable base or scaffold to gain additional height.

Before Use

1. Inspect and make sure all rungs are securely engaged and locked in place. Check that top and bottom rails are firmly supported.
2. Place the ladder on a firm level surface Don't use on slippery surface. Do not place on boxes, unstable base or scaffold to gain additional height.
3. Ensure the ground is free from contaminants Keep ladder clean. Get away from grease, oil mud, snow, wet paint, and other slippery material. Keep your shoes clean.
4. Set the ladder at proper 75 degree angle by bracing ladder based a distance equal to 1/4 of total working length of ladder.
5. Maintain a firm grip. Use both of your hand when climbing, with one more person holding the ladder if possible.
6. Don't over-reach, don't step off the side of the ladder.
7. Do not let the ladder come in contact with live electrical wires
8. When transporting ladders on roof bars or in a truck,ensure they are suitably placed to prevent damage.
9. Inspect the ladder after delivery and before first use to confirm condition and operation of all parts.
10. Do not use a damaged ladder.
11. Remove any contamination from the ladder such as wet paint, mud,oil or snow.



ロックレバー

① カップリング　② スライドラッチ　③ ストラップの固定

④ グリップハンドル　⑤ 滑り止めボトムキャップ　⑥ 滑り止めラング

■使用方法

•伸ばす時

1段ずつステップを地面に水平に持ち上げてもらい、引き伸ばしカチッというまで引き上げてください。

•縮める時

一段ずつロックを解除して縮めます。



ロックを解除する前に、写真のように両手をステップの外側に置いてください。

本体を持ちながらロックを1、2順番通り内側にスライドします。

本体を持ちながらラダーを縮めます。

他の段も同じように全部縮めいき、最後にベルトで固定します。

注）1：
スイッチを誤って落としてしまった場合、交換用のペアスイッチが同梱されています。
穴に差し込むだけで、ラダーが使えるようになります。

※伸縮時の注意

立てた状態のものを1人でロック解除をすると、上のはしごが落ちてきて手や指を挟む危険があります。

2人で作業を行うか傾斜を緩やかにする等、怪我をしないように作業を行ってください。

ご注意、ステップの間に置くと手が挟まれる可能性があります。

▼ 注意事項 ▼

※箱などの足場が不安定な場所に設置しないようにしてください。

※ぬかるみやオイルの散布されたような場所・底面での設置はお控えください。

※作業する際、頭上に注意してください。

※ロックがかかっている事を確認してから使用してください。

※手や指を挟まないよう、特にご注意してお使いください。

※海外輸入商品につき、お届けした商品に、汚れ・ダメージ等が付いている場合がございます。

※当店で販売している伸縮はしごには全てご覧の説明書を同封しておりますので、商品によっては若干の差異がある場合があります、ご了承ください。

安全にお使いいただくために

誤った使い方をされますと重大な事故につながる恐れがあります。
下記を熟読し、ご理解してからご使用ください。

⃠

1. この取扱い説明書に記載されている使用目的以外に使用しないでください。
2. 加工や改造をしないでください。
3. 警告ラベルの内容が理解できない人には使わせないでください。
4. 本製品が変形した場合には使用しないでください。
5. 本製品が安定しない場所には設置しないでください。
6. 本製品が滑りやすい場所には設置しないでください。
7. ドアなどの出入口には設置しないでください。
8. 雨の中や風が強い場所には設置しないでください。
9. 足元や周囲が確認しにくい暗がりには設置しないでください。
10. 台や箱なとの上にのせて使用しないでくたさい。
11. 同時に2人以上で乗らないでください。
12. 昇降を背面で行わないでください。
13. 本製品の支柱から身体を乗り出さないでください。
14. 身体の安定が得られないような荷物を持って、昇降しないでください。
15. 本製品の上で壁や物を無理に押したり、引いたりしないでください。

⚠
指示

1. 設置するときや持ち運ぶときには配電線に注意してください。
2. アルミ製はしごは電気を通しますので、感電にご注意ください。
3. 本製品の耐荷重は150kgです。耐荷重を守って使用してください。
4. 使用に適した服装で使用してください。
5. ご使用前には必ず点検を行い、異常のないことを確認してください。
6. 使用する前に踏ざんのロック状態を必ずご確認ください。
7. 指づめに注意してください。
8. 左右方向転倒に注意してください。

⃠
禁止

1. 疲労、飲酒、病気、妊娠、身体に異常を感じる状態などのときには。
2. 使用しないでください。
3. 持ち運ぶときは引きずったり、投げたりなど乱暴に扱わないでください。
4. 周囲に危険物がある場所や頭上に障害物のある場所には設置しないでください。
5. 慎重に昇り降りして、途中から飛び降りないでください。