



WNL05IP



3.75" x 29.75" x 20" (H x W x D)

30" wide gas cooktop in white with 4 open burners, continuous cast iron grates, and battery start ignition, made in the USA

Highlights:

- Made in the USA
- 30" size fits popular 28 3/8" W x 18 5/8" D counter cutouts
- Battery start ignition is ideal for locations without standard electrical power access

Product Features:

30" Wide Gas Cooktop	Built-in natural gas cooktop with four open burners
Made in the USA	Designed and constructed domestically
Cast iron grates	Two sets of continuous grates in heavy duty cast iron hold up to large cookware
Battery start ignition	Ideal alternative to pilot light sources when no power source is accessible
Electronic/gas spark ignition	Spark ignition system with a pre-installed 115V cord and standard NEMA 5-15P plug
Classic 30" fit	Fits common 28 3/8" W x 18 5/8" D counter cutouts
Four open burners	9000 BTU burners meet most cooking needs
White exterior	Classic design in a clean white finish to match any kitchen
Porcelain finish	Scratch-resistant design for lasting durability



WNL05IP Specifications:

Overview	
Nominal Height	4.0" (10 cm)
Height of Cabinet	3.75" (10 cm)
Nominal Width	30.0" (76 cm)
Width	29.75" (76 cm)
Nominal Depth	20.0" (51 cm)
Depth	20.0" (51 cm)
Cabinet	White
US Electrical Safety	CSA
Weight	27.0 lbs. (12 kg)
Parts & Labor Warranty	1 Year
UPC	761101158228
Gas Cooktop	
Ignition	Battery Start
LP Convertible	With Kit LP Accessory
Number of Burners	4
Controls	Dial
Surface	Painted
Grate Material	Cast Iron
Cutout Width	28.38" (72 cm)
Cutout Depth	18.63" (47 cm)
Burner #1 BTU	9000.0
Burner #2 BTU	9000.0
Burner #3 BTU	9000.0
Burner #4 BTU	9000.0
Power Cord Included	Yes

