



# HRTX18W



4" x 18" x 12" (H x W x D)

18 inch wide under cabinet retractable range hood for ductless use in white, made in the USA

### Highlights:

- Designed and manufactured in the USA
- Low profile 4" height for easy integration in your kitchen
- Engineered specifically for recirculating (ductless) ventilation

### Product Features:

|                                               |                                                                                                                                             |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|
| 18" Wide Retractable Recirculating Range Hood | Slim-fitting low profile range hood ideal for apartments and other small kitchens                                                           |
| Premium design for luxury kitchens            | Retractable filter blends in seamlessly with cabinetry when not in use for an elevated kitchen look                                         |
| Low profile 4" height                         | One of the slimmest under-cabinet hoods in the market, creating a minimalist look that takes up less vertical space than the competition    |
| Designed for ductless operation               | The industry's first range hood specifically made for efficient filtration in recirculating applications with no access to exterior ducting |
| Made in the USA                               | Designed and manufactured by Summit in the USA, complete with American steel for lasting durability                                         |
| Improved filtration with smoother airflow     | Unique cross-flow fan moves up to 40% more air through the filters than standard hoods converted to recirculating mode                      |
| Angled airflow keeps smoke away from user     | Vents are set at a slight upwards angle, ensuring smoke and odors won't be directed towards the home cook                                   |
| Quality construction for long-lasting use     | Metal ball-bearing glides, innovative cross-flow fan, and steel materials to ensure efficient use for years of reliable ventilation         |



## HRTX18W Specifications:

| Overview                   |                  |
|----------------------------|------------------|
| Height of Cabinet          | 4.0" (10 cm)     |
| Width                      | 18.0" (46 cm)    |
| Depth                      | 12.0" (30 cm)    |
| Depth with door at 90°     | 18.25" (46 cm)   |
| US Electrical Safety       | ETL              |
| Canadian Electrical Safety | ETL-C            |
| Amps                       | 1.7              |
| Voltage/Frequency          | 115 V AC/60 Hz   |
| Weight                     | 18.0 lbs. (8 kg) |
| Parts & Labor Warranty     | 1 Year           |
| UPC                        | 761101154701     |
| Range Hood                 |                  |
| Installation               | Under Cabinet    |
| Venting                    | Recirculating    |
| Controls                   | Dial             |
| Light                      | Yes              |
| Number of Lights           | 2                |
| Light Type                 | LED              |
| Number of Fan Speeds       | 2                |

