

BEN

F6732-VGL

Evoking the natural beauty of the coast, the Ben chandelier features a cascading silhouette with intricate, handmade detailing. Strings of wooden beads form fluid tiers that move gently, creating a dappled lighting effect. A woven abaca wrap ring anchors the design, which is available in two sizes. Vintage Gold Leaf fittings balance the organic textures with a bright detail.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 25.75"
Width/Diameter: 32"
Minimum Height: 38"
Maximum Height: 97.75"
Canopy/Backplate: 4.75"
Hanging Type: 144" Braided Cord
Product Weight: 28.6lb
Canopy/Backplate Shape: Round
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Tree Derived
Shade 1 Finish: Wood Beads
Shade 1 Height: 11"
Shade 2: Tree Derived
Shade 2 Finish: Wood Beads
Shade 2 Height: 10.75"

ELECTRICAL



Bulb 1

Bulb Included: No
Socket: E12 Candelabra Base
Bulb Type: B11
Max Wattage: 10
Bulb Quantity: 4
Wire Length: 144"
Cord Type: SVT CREAM FABRIC
Gem Box Required (2"x3") : No
Dark Sky: No

SHIPPING

Carton 1: 36" x 36" x 26"
Carton 1 Weight: 41lb
Shipping Method: Truck Only
Country of Origin: PH

