

2KV DIESEL LOCOMOTIVE CABLE

Flexible power leads for installation in conduit



GENERAL INFO

No longer are industrial cord products used only in coal mines and industrial plants; today typical applications include providing temporary power to job sites, as well as flexible power leads for installation in conduit. General Cable's role, as the producer of the premiere Carol® Brand industrial cord products, is to ensure that new product development, product innovation and quality not only keep pace with industry requirements but also set the trends. Our industrial cord products carry a full range of listings and certifications with Underwriters Laboratories, Inc. and the Canadian Standard Association. In addition, many products meet or exceed the requirements of UL, CSA, OSHA, MSHA, ICEA and other relevant industry standards. Carol is simply the most accepted brand in the industry, having proven itself on the job time after time. Our industrial cord line is the most comprehensive in the industry, ensuring that the proper Carol product can always be specified.

CONSTRUCTION/DESIGN

Nominal outer diameter [inch]	Conductor strand count	Cable marking	Conductor category	AWG size
				28
0.065	2318W	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Class 2 = stranded	Other
0.065	2318W	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Class 2 = stranded	Other
0.065	2318W	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Class 2 = stranded	Other
0.065	2318W	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Class 2 = stranded	Other
0.065	2318W	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Class 2 = stranded	Other
		GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Class 2 = stranded	Other
1	650W	CAROL SUPER VU-TRON® (SIZE) 90°C DLO 2000 V P-102 MSHA CSA RW90 1000 V (-40°C) FT1 SR TC		
0.065	2318W	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Class 2 =	Other

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
14003.016	262C MCM DIESEL LOCOMOTIVE CABLE BLK		28	NA	1	Black
5310.01004	4C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01110M	1/0C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01262	262.6C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.0131	3/0C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01210M	2/0C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
91926.99.01	262.6C DIESEL LOCOMOTIVE CABLE BLK	CAROL SUPER VU-TRON® (SIZE) 90°C DLO 2000 V P-102 MSHA CSA RW90 1000 V (-40°C) FT1 FT4 SR TC	Other	NA	1	Black
5310.01313	313.1C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01313M	313.1C MCM DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01001	1C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
5310.01444	444.4C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07- KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01001M	1C AWG DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07- KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01373	373.7C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07- KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.0121	2/0C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07- KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01410M	4/0C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07- KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01008	8C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07- KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5330.0121	2/0C DIESEL LOCOMOTIVE CABLE BLK		Other	NA	1	Black
5310.01006	6C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07- KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01444M	444.4C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07- KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01262M	262.6C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07- KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
5310.01310M	3/0C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
14003.0151	1/0C AWG DIESEL LOCOMOTIVE CABLE BLK	PRYSMIAN GROUP (H) (YEAR) EASY GLIDER(R) THHN/THWN-2 (UL) E66903 10 AWG (5.26 MM2) GR I AND GR II 600V VW-1 OR T90 NYLON / TWN75 C(UL) FT1 (-25C)	Other	NA	1	Black
5310.01002	2C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.0141	4/0C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01002M	2C AWG DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.01373M	373.7C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black
5310.0111	1/0C DIESEL LOCOMOTIVE CABLE BLK	GENERAL CABLE® (MFG LOCATION) DIESEL LOCOMOTIVE 2000 V P-07-KA120005-MSHA C(UL)US TYPE RHH OR RHW-2 VW-1 (SIZE) AWG/kcmil (MM2) EP FOR CT USE* SR -40°C FT4 OR RW90 EP 1000 V ROHS MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK *Applicable for sizes 1/0 AWG and larger only	Other	NA	1	Black

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
14003.016	262C MCM DIESEL LOCOMOTIVE CABLE BLK							
5310.01004	4C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.01110M	1/0C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.01262	262.6C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.0131	3/0C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.01210M	2/0C DIESEL LOCOMOTIVE CABLE BLK		0.08				2	
91926.99.01	262.6C DIESEL LOCOMOTIVE CABLE BLK		0.095	1			2.41	25.4
5310.01313	313.1C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.01313M	313.1C MCM DIESEL LOCOMOTIVE CABLE BLK		0.09	1			2.3	25.4
5310.01001	1C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
5310.01444	444.4C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.01001M	1C AWG DIESEL LOCOMOTIVE CABLE BLK		0.08	0.64			2	16.26
5310.01373	373.7C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.0121	2/0C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.01410M	4/0C DIESEL LOCOMOTIVE CABLE BLK		0.08	0.84			2	21.3
5310.01008	8C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5330.0121	2/0C DIESEL LOCOMOTIVE CABLE BLK							
5310.01006	6C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.01444M	444.4C DIESEL LOCOMOTIVE CABLE BLK		0.09	1.11			2.3	28.2
5310.01262M	262.6C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.94			2.3	23.9

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
5310.01310M	3/0C DIESEL LOCOMOTIVE CABLE BLK		0.08	0.8			2	20.32
14003.0151	1/0C AWG DIESEL LOCOMOTIVE CABLE BLK							
5310.01002	2C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.0141	4/0C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.01002M	2C AWG DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7
5310.01373M	373.7C DIESEL LOCOMOTIVE CABLE BLK		0.09	1.06			2.3	26.9
5310.0111	1/0C DIESEL LOCOMOTIVE CABLE BLK		0.09	0.065			2.3	1.7

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	14003.016	262C MCM DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.01004	4C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.01110M	1/0C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.01262	262.6C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.0131	3/0C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.01210M	2/0C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	91926.99.01	262.6C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO	1,130	LBS
	5310.01313	313.1C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.01313M	313.1C MCM DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.01001	1C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	5310.01444	444.4C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.01001M	1C AWG DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.01373	373.7C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.0121	2/0C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.01410M	4/0C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.01008	8C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5330.0121	2/0C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.01006	6C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.01444M	444.4C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.01262M	262.6C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	5310.01310M	3/0C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	14003.0151	1/0C AWG DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.01002	2C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.0141	4/0C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTS		LBS
	5310.01002M	2C AWG DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.01373M	373.7C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS
	5310.0111	1/0C DIESEL LOCOMOTIVE CABLE BLK	US	Distribution products	MTO		LBS

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
14003.016	262C MCM DIESEL LOCOMOTIVE CABLE BLK	FOOT	0	0	0	Long Length Reel
5310.01004	4C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01110M	1/0C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01262	262.6C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	48	Factory Reel
5310.0131	3/0C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01210M	2/0C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	100 FT Spool
91926.99.01	262.6C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01313	313.1C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	48	Factory Reel
5310.01313M	313.1C MCM DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Clamshell
5310.01001	1C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
5310.01444	444.4C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01001M	1C AWG DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01373	373.7C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	48	Factory Reel
5310.0121	2/0C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	48	Factory Reel
5310.01410M	4/0C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01008	8C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5330.0121	2/0C DIESEL LOCOMOTIVE CABLE BLK	FOOT	0	0	0	Long Length Reel
5310.01006	6C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	48	Factory Reel
5310.01444M	444.4C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01262M	262.6C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	100 FT Spool

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
5310.01310M	3/0C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Clamshell
14003.0151	1/0C AWG DIESEL LOCOMOTIVE CABLE BLK	FOOT	0	0	0	Long Length Reel
5310.01002	2C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.0141	4/0C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01002M	2C AWG DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel
5310.01373M	373.7C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Clamshell
5310.0111	1/0C DIESEL LOCOMOTIVE CABLE BLK	FOOT	48	42	1	Factory Reel