

Project Name

Location

Prepared By



Notes

(www) 01-20-2023 09:30:19

General	
Status	Active
Watts	3.5W
Fluorescent Equivalent	5W/7W/9W
Volts	120V-277V
Ballast Type	Type B
Shape	PL
Base	2G7
ANSI Base	2G7
Finish	Frost
CCT (Kelvin)	2700K/3000K/3500K/4000K
Temperature	Warm to Cool White
CRI	80
Lumens	380L/390L/400L/410L
Beam Spread	120
Dimmable	Non-Dimmable
Hours Rated	50000
Operating Position	Universal
Technology	LED

Electrical	
Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical	
MOL	4.74
MOD	1.26
Weight (lb.)	0.06

Additional Information	
Rated For Enclosed Fixture	No
Warranty	5 Year Limited - 10 hr per day

Compliance	
Safety Listing	cULus - Classified
Location Rating	Damp
NSF Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes