SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

60-8741 - Cassian; 1 Light Wall Sconce; Satin Brass Finish; Opal Glass

DAMP LOCATION | ETL | FC | RoHS | 30,000 HOURS | 1 YEAR WARRANTY | 120 VOLT | IP 20

GENERAL

Company	NUVO
EA Height	10.0
EA Width	8.0
EA Length	10.0
Mounting Height	16.13
Mounting Length	4.75
Mounting Width	6.13
Glass Finish	Opal
Extends (in)	6.13
Material	Steel / Glass
Includes	Mounting Strap and Screws
Status	Active
Style	Modern and Contemporary
Top To Outlet	8.0
Up Down Installation	Universal
CCT Selectable	No
Wattage Selectable	No
Collection	Cassian
Finish Family	Brass
Indoor Outdoor	Indoor
Product Technology	Lamp Dependent
Fixture Lamp Count	1
Fluor Equiv	8W
Incandescent Equivalent	45W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	Lamp Dependent
Dimmable	Lamp Dependent
Hours Rated	30000
Operating Temp	-40F to +194F (-40C to +90C)
Volts	120v
Watts	6.5W
Connection	Hardwire

PHYSICAL

Lamp Base	G9 Double Loop
Finish	Satin Brass
Housing Color	Satin Brass
ANSI Base	G9
Lamp Type	T6
Fixture Shape	Round

ADDITIONAL INFO

Warranty	1-Year
Rated For Enclosed Fixture	No

PACKAGING

UPC	045923416675
Case Cube	0.463
Case Height	10.0
Case Length	10.0
Case Quantity	1
Case UPC	10045923416672
Case Weight	2.86
Case Width	8.0
EA Cube	0.463
EA Height	10.0
EA Length	10.0
EA Quantity	1
EA Weight	2.86
EA Width	8.0
Pack Type	Kraft Box
Web Height	16.13
Web Width	4.75

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026