Project / Job Name:

Location:

Fixture Type:

Notes:

65-655 - 29 Watt Small LED Wall Pack with Integrated Bypassable Photocell; CCT Selectable; 120-277 Volts; Dusk to Dawn Security Lighting; IP65; Bronze Finish

GENERAL

Company	NUVO
EA Height	9.65
EA Width	10.19
EA Length	9.88
Bulb Included	Integrated
Extends (in)	7.45
Material	Aluminum / Polycarbonate (PC)
Fixture Type	Wall Pack
Status	Active
Style	Traditional
Surge Protection	Built-in surge protection - 2.5KV
Total Harmonic Distortion	15%
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	Bronze
Additional Info	IK10 Lens
Amps	0.242-0.105A
Has Camera	No
Integrated Features	Integrated Photocell
IOT Enabled	No
Photo Cell	Yes - Bypassable
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	200W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	80
Color Temp	Warm to Cool White
CRI	70+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40F to +113F (-40C to +45C)
HID Equivalent	125W
Lumens	3650L-3770L
Volts	120V-277V
Watts	29W
Max Lumens	3770L
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Wall

ADDITIONAL INFO

Warranty	5-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923651755
Case Cube	2.6229
Case Height	20.28
Case Length	20.28
Case Quantity	4
Case UPC	10045923651752
Case Weight	21.38
Case Width	11.02
EA Cube	0.5622
EA Height	9.65
EA Length	9.88
EA Quantity	1
EA Weight	5.35
EA Width	10.19
Pack Type	Box
Web Height	8.44
Web Width	8.5

COMPLIANCE

ADA Compliant	No
Bug Rating	B1-U3-G2
CA Prop 65	Lead
DLC ID	PLUFWGU0SVE7
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026