



jalas® VIP 2128

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2011 S3, SRA, HRO

Learn more

LOOK GOOD, FEEL SAFE

A brown classic mid-cut business boot in leather combined with a safety shoe. Discreet pattern on the upper side. For proper dress both in the office and in the factory. Toe cap in steel, textile nail protection insert and anti-slip shock absorbing outsole. Available in both men's and women's sizes.

CHARACTERISTICS

- Good fit
- Comfortable
- Excellent shock absorption

FUNCTIONS

- Anti-static properties
- Ventilating insole
- Water repellent leather
- Specially designed details
- Shock absorbing
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Prevents risk of: , Toe injuries, Nail penetration, Sprain injuries, Antistatic, Strain injuries

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, Office environments, Environments with risk for outsole penetration, Dry environments, Clean environments

PRIMARY AREAS OF USE

Engineering, Office work

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Narrow/Regular
COLLECTION VIP
UPPER MATERIAL Full-grain leather
TOECAP MATERIAL Steel
INSOLE JALAS 8218 FX2 VIP Safety
INNERSOLE MATERIAL Leather, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING Laces
SHOELACES LENGTH 100 cm
COLOUR Brown
NET WEIGHT, (SIZE 42) 1.41 kg

COMPLIANCE

CE Cat. II

ASTM F2413-18
M/I/C/SD 35/PR

EAC

EN ISO 20345:2011
S3, SRA, HRO

TP TC 019:2011

FEATURES

- Anti-static properties
- ESD
- Oil-resistant outsole
- Nail protection in plasma-treated composite (PTC) textile
- Shock absorbing
- Steel toecap
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	2128-35	6408487509698
36	3	4	5	2128-36	6408487509704
37	4	5	6	2128-37	6408487509711
38	5	5.5	6.5	2128-38	6408487509728
39	6	6.5	7.5	2128-39	6408487509735
40	6.5	7.5	8.5	2128-40	6408487509742
41	7	8	9	2128-41	6408487509759
42	8	9	10	2128-42	6408487509766
43	9	9.5	11	2128-43	6408487509773
44	10	10.5	11.5	2128-44	6408487509780
45	10.5	11	12.5	2128-45	6408487509797
46	11	12	13	2128-46	6408487509803
47	12	13	14	2128-47	6408487509810
48	13	13.5	14.5	2128-48	6408487509827

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.