



025-1688 through 025-1694

Contour Full Body Harness: 1D, QC Chest, TB Legs

FEATURES:

- More adjustability for a secure fit on a wide range of body types
- Ergonomic shoulder pad for balanced weight distribution
- Precise chest strap alignment for comfort and security
- Lightweight padding with superior airflow for all-day comfort
- Fixed dorsal D-ring
- Integrated SRL channel
- Quick-connect chest
- Two mating buckle torso adjusters on each side
- Tongue buckle legs
- Breakaway lanyard keepers

FALL ARREST POINT(S):

- 1 Dorsal D-ring
- 1 Integrated SRL Channel

ITEM WEIGHT:

- 4.2 lbs. (1.9 kg)



DORSAL ATTACHMENT

USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.11-2021
OSHA	1926.502, 1910.140

SIZE(S)	
025-1688	X-Small
025-1689	Small
025-1690	Medium
025-1691	Large
025-1692	X-Large
025-1693	2X
025-1694	3X

COMPONENT	MATERIAL SPECIFICATION
Webbing	Polyester
D-ring (s)	Zinc-plated steel
Adjuster buckles	EP coated steel
Chest connection	EP coated steel
Leg connection	Zinc-plated steel buckle w/SS grommets
SRL channel	TPU, polycarbonate
Pads	Polyester, EVA, vinyl