



# msi

## MONITOR OPTIX MAG271R



### SPECIFICATIONS

<b>Panel Size</b>	27"
<b>Panel Resolution</b>	1920 x 1080 (FHD)
<b>Refresh Rate</b>	165Hz
<b>Response time</b>	1ms (MPRT)
<b>Brightness (nits)</b>	300
<b>Viewing Angle</b>	178° (H) / 178° (V)
<b>Aspect Ratio</b>	16:9
<b>Contrast Ratio</b>	3000:1
<b>DCR</b>	100000000:1
<b>Active Display Area (mm)</b>	597.6 (H) x 336.15 (V)
<b>Pixel Pitch (H x V)</b>	0.3114 (H) x 0.3114 (V)
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	16.7M
<b>DCI-P3 / sRGB</b>	92% / 118%
<b>Video ports</b>	1x DP (1.2) 2x HDMI (2.0) 2x USB 2.0
<b>USB ports</b>	1x USB 2.0 Type B
<b>Audio ports</b>	1 x Earphone out
<b>Kensington Lock</b>	Yes
<b>VESA Mounting</b>	100 x 100 mm
<b>Control</b>	5-way OSD navigation joystick
<b>Power Type</b>	External Adaptor 12V 5A
<b>Power Input</b>	100~240V, 50~60Hz
<b>Signal Frequency</b>	30 to 160KHz(H) 60 to 165Hz(V)
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Height)</b>	0 ~ 130 mm
<b>Dimension (W x H x D)</b>	617 x 182.4 x 535.3 mm / 24.29 x 7.18 x 21.07 inch 720 x 575 x 155 mm / 28.35 x 22.64 x 6.1 inch
<b>Weight (NW / GW)</b>	6.68kg;14.73lbs / 7.3kg;16lbs
<b>Frameless Design</b>	Yes
<b>Note</b>	Display Port: 1920 x 1080 (Up to 165Hz) HDMI: 1920 x 1080 (Up to 165Hz)

### FEATURES

- FHD High Resolution - Game titles will even look better, displaying more details due to the FHD resolution.
- 165Hz Refresh Rate - Real smooth gaming.
- 1ms response time - eliminate screen tearing and choppy frame rates.
- Gaming OSD App - Create the ultimate viewing settings for your game.
- Mystic Light - The ultimate gaming finish.
- True colors - DCI-P3 92% & sRGB 118%.
- AMD FreeSync - prevent screen tearing.
- Anti-Flicker and Less Blue Light - game even longer and prevent eye strain and fatigue.
- Frameless design - Ultimate gameplay experience.
- 178° wide view angle.