
Curvo | E22924-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION



*max overall height

MEASUREMENTS

DIMENSION	: 38.75" L x 38.75" W x 6.75" H
MAX OAH	: 129" OAH
CANOPY	: 8.75" W x 1.75" H x 8.75" L
HANGING WEIGHT	: 9.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 6,400 Rated (2,200 Del.)
BULB	: 1 x 80W LED DC Integrated , 80W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum, Steel, Silicone

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com