



Fibre-Metal®

Type II Vented, Full Brim Industrial Climbing Helmet with HDPE Shell, 8-Point Textile Suspension, Wheel Ratchet Adjustment and a 4-Point Chinstrap

- Full brim shell design provides protection from the elements when working outdoors
- Liquid Crystal Polymer (LCP) yarn in the six strap, eight-point suspension disperses force transferred from the shell to the user
- Non-Newtonian foam combined with a traditional EPS foam liner
- One-way moisture transfer and fast-dry chin strap help elevate user comfort in high-temperature work environments, by providing a dry and comfortable feel
- Compatible with a wide range of safety accessories such as a welding helmet, visor, faceshield, UV shade, earmuffs, or task light
- ANSI/CSA Certified, Type II, Class C

Technical Data

Color	White, Gray, Multi, Green, Yellow, Black, Dark Blue, Orange, Red, Brown
Sizes Available	OS
Packaging	Bagged Each
Packed	1/Case
Case Weight (lbs)	0.00
Country of Origin	China
Shell Material	HDPE
Shell	Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Chin Strap	4-Point Polyester
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified

Performance Data

ANSI Type	Type II
Electrical Class	Class C

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
CSH13011	Black	OS	883940457390		
CSH13012	Brown	OS	883940457383		
CSH13071	Dark Blue	OS	883940457352		
CSH13009	Gray	OS	883940457321		
CSH13004	Green	OS	883940457345		
CSH13080	Multi	OS	883940457406		
CSH13046	Orange	OS	883940457369		
CSH13015	Red	OS	883940457376		
CSH13001	White	OS	883940457314		
CSH13002	Yellow	OS	883940457338		