



PIP® PosiGrip®

Unsupported Nitrile, Flock Lined with Raised Diamond Grip - 18 Mil

- Medium weight construction and hand specific design provide real comfort with protection
- Provides flexibility, tactile sensitivity and dexterity sometimes lacking in heavier gauge unsupported nitriles
- Provides the protection from chemical and physical hazards not always found in thinner gauge nitrile disposables
- Flock lining provides increased comfort and ease of donning
- Straight cuff adds additional length to protect the forearm from liquid run-off
- Raised Diamond pattern for an enhanced grip

Applications

- Cleaning
- Laboratory Analysis
- Printing Industries
- Agrochemicals
- Assembly



4101XX AJKLMNOPT

Technical Data

Color	Green
Sizes Available	8-11
Polymer	Nitrile
Thickness	18 Mil
Lining	Flocked
Length	13"
Cuff	Straight
Grip	Raised Diamond
Construction	Unsupported
Case Dimensions (in)	11.42 x 12.99 x 14.17
Case Weight (lbs)	28.66
Packed	12 Dozen/Case
Packaging	Bulk Pack
Certifications	21 CFR
Country of Origin	Sri Lanka

Performance Data

EN 374	AJKLMNOPT
EN 388	4101XX

Care Instructions



Do Not Wash

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
52N104/8	Green	8	662909024657	20662909024651	10662909024654
52N104/9	Green	9	662909024664	20662909024668	10662909024661
52N104/10	Green	10	662909024671	20662909024675	10662909024678
52N104/11	Green	11	662909024688	20662909024682	10662909024685